

**PIONEERING TECHNOLOGIES  
AND REVOLUTIONARY  
THERAPIES FOR THE  
ULTIMATE TREATMENT  
EXPERIENCE IN UROLOGY.**

CONTACT INTERMED RESOURCES TN  
TODAY TO CONNECT TO YOUR  
REPRESENTATIVE FOR  
FURTHER INFORMATION.

**Leading Technology. Improving Life.**



**1-800-224-6113**  
**support@intermedtn.com**  
**www.intermedtn.com**

# **COMPREHENSIVE UROLOGY PORTFOLIO**

YOUR **ONE** UROLOGY SOURCE

STONE MANAGEMENT LASERS



**Solvo® H35**  
ADVANCED MODE®  
REDUCED  
RETROPULSION



**H100**  
HIGH HERTZ  
STONE DUSTING



**H140**  
HIGHEST POWER  
AND SPEED



**THULIO®**  
ADVANCED  
THULIUM  
TECHNOLOGY




COMPACT  
**SIGMA®**  
MODULAR  
LITHOTRIPTER



**DELTA® III**  
WORLD'S BESTSELLING  
LITHOTRIPTER

ESWL®

UROLOGY TABLE



**NAUTILUS®**  
NEXT GENERATION  
MULTIPURPOSE TABLE


STONE MANAGEMENT PRODUCTS

VISUALIZE



**AXIS**  
SINGLE-USE DIGITAL  
UTEROSCOPE

BREAK & DUST



**HOLMIUM LASER FLEXFIBERS®**  
FEATURING GENTLEFLEX® BALL TIP FIBERS  
200µm - 1000µm

**THULIO LASER PERFORMANCE FIBERS**  
FEATURING BALL TIP FIBERS  
200µm - 1000µm

DILATE

**EQUINOX**  
DILATATION  
BALLOON  
CATHETER



BIPOLAR SALINE ELECTRODES  
RESECT & VAPORIZE

**DISC™**  
VAPORIZATION  
ELECTRODE

MEDIUM  
**CUTTING  
LOOP**

LARGE  
**CUTTING  
LOOP**


**NEEDLE**

**BLADDER  
LOOP**




RETRIEVE

**VENUS**  
GRASPER  
BASKET



**ECLIPSE**  
ZERO TIP  
BASKET



**HALO**  
BASKET



**TETRA**  
STANDARD  
BASKET



**XPAND**  
INFLATION  
DEVICE



ACCESS

**SLIP**  
RETRIEVAL  
WIRE



**MERIDIAN**  
GUIDEWIRE



**APOLLO**  
GUIDEWIRE



**MAGELLAN**  
ACCESS  
SHEATH




**MINNOW**  
URETERAL  
CATHETER



DRAIN

**CASCADE**  
URETERAL  
STENT





## THULIO

100W High Power Advanced Thulium Laser with **RealPulse**<sup>®</sup> Technology for Stones and BPH

**55%** more control<sup>1</sup> with CAPTIVE<sup>®</sup> MODE

Our fragmenting mode offers virtually no retropulsion

**7x** the PEAK POWER<sup>2</sup>

Driving an enhanced fragmentation experience

**3x** the SPEED<sup>3</sup>

300 Hz frequency and excellent fine dusting capabilities<sup>3</sup>

# One Laser for Stones and BPH

## Captive® Mode



**Captive®  
Fragmenting mode**  
*Virtually no retro-pulsion*



**Fragmenting  
mode**



**Dusting mode**



**Enucleation  
mode**



**Soft Tissue  
mode**

## Thulio's Pre-set Application Modes

## Ergonomic and User-Friendly Display

- Easy-to-navigate interface with large, rotatable touchscreen.
- Effortlessly toggle between pre-selected settings using dual footswitch and split-screen interface.



**DANGER**  
VISIBLE AND INVISIBLE LASER RADIATION  
AVOID EYE OR SKIN EXPOSURE TO  
DIRECT OR SCATTERED RADIATION  
CLASS 4 LASER PRODUCT (IEC0825-1:2014-05)



## Powerful and Compact Laser

- 100 watts of power in a small, convenient footprint.
- Lightweight and highly portable for ease of use.

## Smart, Dual Footswitch

- Switch seamlessly from one pre-defined mode to another.
- Easily adjust parameter settings with ergonomic footswitch.

